


DRY AGER® DX500® PREMIUM S


for up to 20 kg load

Drawings

Front view




Top view




Integration drawings


Installation of one device



Installation of several devices (on top)



Installation of several devices (side by side)



- ① Ventilation shaft is mandatory. Minimum size: **200 cm²**. Also possible on the side or on the back wall.
- ② Overall dimensions (width) with the door open including handle: **615 mm**
- ③ Overall dimensions (depth) body + closed door (protruding): **610 mm**
- ④ Panelling of the intermediate gap with DRY AGER® stainless steel cover possible (DX0031).

